

TRAVELLING TROLLEYS Corso Trolley

- Model from 250kg to 20 000kg
- Rolls on sealed-for-life ball bearings
- Easy adjustment to the size of the steel beam using crank
- Wide adjustment range
- Bumper stop and derailment guard
- Tipping guard
- Movement is achieved through pushing
- Movement is achieved through an endless chain drive
- Motorised movement



Model	WLL	Dimensions		Mini Radius curve (mm)	Nominal effort on chain (N)	Weight of push trolley (kg)	Weight of chain operated trolley (kg)
		traverse bar 1 (mm)	traverse bar 2 (mm)				
250	250 kg	45 - 152	-	650	-	3,5	-
500	500 kg	50 - 220	220 - 300	900	*	8,5	-
1000	1000 kg	58 - 220	220 - 300	1000	55	10,5	19
2000	2000 kg	66 - 220	220 - 300	1200	100	18	22,5
3000	3000 kg	74 - 220	220 - 300	1300	75	32	37,5
5000	5000 kg	90 - 220	220 - 300	1400	120	48,5	55
10000	10000 kg	142 - 320	-	2500	200	110	120
20000	20000 kg	153 - 320	-	5000	2 x 255	-	245